






















# Quatro

Extract fans with decorative front panel

- Motor type: AC
- Timer: Turn off timer
- Humidity sensor
- Casing material: Plastic




Lineup	Connected air duct size, mm	Maximum airflow, m <sup>3</sup> /h	Sound pressure level LpA at 3 m, dB(A)	Rated power, W	Pull cord	Timer	Humidity sensor
 Quatro 100	100	88	33				
 Quatro 100 S	100	88	33	14	✓		
 Quatro 100 T	100	88	33	14		✓	
 Quatro 100 ST	100	88	33	14	✓	✓	
 Quatro 100 H	100	88	33			✓	✓
 Quatro 100 SH	100	88	33	14	✓	✓	✓

 Quatro 125	125	167	34				
 Quatro 125 S	125	167	34	16	✓		
 Quatro 125 T	125	167	34	16		✓	
 Quatro 125 ST	125	167	34	16	✓	✓	
 Quatro 125 H	125	167	34	16		✓	✓
 Quatro 125 SH	125	167	34	16	✓	✓	✓
 Quatro 150	150	265	37	24			
 Quatro 150 S	150	265	37	24	✓		
 Quatro 150 T	150	265	37	24		✓	
 Quatro 150 ST	150	265	37	24	✓	✓	
 Quatro 150 H	150	265	37	24		✓	✓
 Quatro 150 SH	150	265	37	24	✓	✓	✓
 Quatro Hi-Tech Chrome 100	100	88	33				

 Quatro Hi-Tech Chrome 100 S	100	88	33	14	✓		
 Quatro Hi-Tech Chrome 100 T	100	88	33	14		✓	
 Quatro Hi-Tech Chrome 100 ST	100	88	33	14	✓	✓	
 Quatro Hi-Tech Chrome 100 H	100	88	33	14		✓	✓
 Quatro Hi-Tech Chrome 100 SH	100	88	33	14	✓	✓	✓
 Quatro Hi-Tech Chrome 125	125	167	34				
 Quatro Hi-Tech Chrome 125 S	125	167	34	16	✓		
 Quatro Hi-Tech Chrome 125 T	125	167	34	16		✓	
 Quatro Hi-Tech Chrome 125 ST	125	167	34	16	✓	✓	
 Quatro Hi-Tech Chrome 125 H	125	167	34	16		✓	✓
 Quatro Hi-Tech Chrome 125 SH	125	167	34	16	✓	✓	✓
 Quatro Hi-Tech Chrome 150	150	265	37				
 Quatro Hi-Tech Chrome 150 S	150	265	37	24	✓		

 Quatro Hi-Tech Chrome 150 T	150	265	37	24		✓	
 Quatro Hi-Tech Chrome 150 ST	150	265	37	24	✓	✓	
 Quatro Hi-Tech Chrome 150 H	150	265	37	24		✓	✓
 Quatro Hi-Tech Chrome 150 SH	150	265	37	24	✓	✓	✓
 Quatro Hi-Tech 100	100	88	33				
 Quatro Hi-Tech 100 S	100	88	33	14	✓		
 Quatro Hi-Tech 100 T	100	88	33	14		✓	
 Quatro Hi-Tech 100 ST	100	88	33	14	✓	✓	
 Quatro Hi-Tech 100 H	100	88	33	14		✓	✓
 Quatro Hi-Tech 100 SH	100	88	33	14	✓	✓	✓
 Quatro Hi-Tech 125	125	167	34				
 Quatro Hi-Tech 125 S	125	167	34	16	✓		
 Quatro Hi-Tech 125 T	125	167	34	16		✓	

 Quatro Hi-Tech 125 ST	125	167	34	16	✓	✓	
 Quatro Hi-Tech 125 H	125	167	34	16		✓	✓
 Quatro Hi-Tech 125 SH	125	167	34	16	✓	✓	✓
 Quatro Hi-Tech 150	150	265	37				
 Quatro Hi-Tech 150 S	150	265	37	24	✓		
 Quatro Hi-Tech 150 T	150	265	37	24		✓	
 Quatro Hi-Tech 150 ST	150	265	37	24	✓	✓	
 Quatro Hi-Tech 150 H	150	265	37	24		✓	✓
 Quatro Hi-Tech 150 SH	150	265	37	24	✓	✓	✓
 Quatro 100 (127-220V/60Hz)	100						
 Quatro 125 (127-220V/60Hz)	125						
 Quatro 150 (127-220V/60Hz)	150						
 Quatro Hi-Tech Chrome 100 (127-220V/60Hz)	100						

 Quatro Hi-Tech Chrome 125 (127-220V/60Hz)	125						
 Quatro Hi-Tech Chrome 150 (127-220V/60Hz)	150						
 Quatro Hi-Tech 100 (127-220V/60Hz)	100						
 Quatro Hi-Tech 125 (127-220V/60Hz)	125						
 Quatro Hi-Tech 150 (127-220V/60Hz)	150						